


**B0612H1005 Cannulated Shaver/Microdebrider**

Ø 0.65 inch • Brushless Slotted • 48 V



MOTOR LEADS:  
6.0 [152] MIN LONG,  
24 AWG STRANDED

HALL SENSOR LEADS:  
6.0 [152] MIN LONG,  
26 AWG STRANDED

Dimensions in inches [mm]

Electrical Data	Symbol	SMX B0612H1005	Unit
1 Nominal Voltage	$U_N$	48.0	Volt
2 Optimization Direction	-	Bi-Directional	-
3 No Load Speed	$n_0$	35,300	rpm
4 Typical No Load Current	$I_0$	125	mA
5 Max. Continuous Mechanical Power (@25°C)	$P_{max}$	68.5	W
6 Max. Continuous Current	$I_{cs}$	1.80	A
7 Max. Continuous Torque	$T_{cs}$	19.6 (2.78)	mNm (oz-in)
8 Back EMF Constant	$k_E$	1.33	V/1000 rpm
9 Torque Constant	$k_T$	12.71 (1.8)	mNm/A (oz-in/A)
10 Motor Regulation	$R/k^2$	13321	$10^3/Nms$
11 Peak Torque	$T_{pk}$	141.7 (20.1)	mNm (oz-in)
12 Motor Constant	$k_M$	8.69 (1.23)	mNm/W <sup>1/2</sup> (oz-in/W <sup>1/2</sup> )
13 Line to Line Resistance	$R_L$	2.152	ohms
14 Inductance Phase to Phase	$L$	0.525	mH
15 Mechanical Time Constant	$T_m$	0.80	ms
16 Electrical Time Constant	$T_e$	0.244	ms

General Data			
17 Gearhead Ratio	-	N/A	Ratio
18 Ambient Working Temperature Range	-	25 (77)	°C (°F)
19 Max Operating Temperature Range	-	155 (311)	°C (°F)
20 Radial Static Force w/o Shaft Support (max)	-	25.99	lbs
21 Axial Static Force w/o Shaft Support (max)	-	10.33	lbs
22 Thermal Resistance	$R_{th}$	12.0	°C/W
23 Thermal Time Constant	$T_w$	936	s
24 Weight	-	75.8 (2.67)	g (oz)
25 Rotor Inertia	$J_m$	9.79 (13.86)	kg-cm <sup>2</sup> 10 <sup>-4</sup> (oz-in-sec <sup>2</sup> 10 <sup>-6</sup> )
26 Hall Sensor Electrical Phasing*	-	60	Electrical °
27 Autoclave Cycles	-	1000+	Cycles

\*Also available without Hall sensors

Wire	Description
Blue	Phase A
Brown	Phase B
Violet	Phase C
Red	4.5 to 24 Vdc
Yellow	Sensor 1
Orange	Sensor 2
White	Sensor 3
Black	GND

