


B1210N1026 Large Bone Orthopedic Saw/Reamer

Ø 1.24 inch • Brushless Slotted • 12 V



Electrical Data		Symbol	SMX B1210N1026	Unit
1	Nominal Voltage	U_N	12.0	Volt
2	Optimization Direction	-	Bi-Directional	-
3	No Load Speed	n_o	14,740	rpm
4	Typical No Load Current	I_o	940	mA
5	Max. Continuous Mechanical Power (@25°C)	P_{max}	126.0	W
6	Max. Continuous Current	I_{cs}	13.0	A
7	Max. Continuous Torque	T_{cs}	80.8 (11.44)	mNm (oz-in)
8	Back EMF Constant	k_E	0.759	V/1000 rpm
9	Torque Constant	k_T	7.25 (1.03)	mNm/A (oz-in/A)
10	Motor Regulation	R/k^2	1084	$10^3/Nms$
11	Peak Torque	T_{pk}	1518.6 (215)	mNm (oz-in)
12	Motor Constant	k_M	30.36 (4.30)	mNm/W ^{1/2} (oz-in/W ^{1/2})
13	Line to Line Resistance	R_L	0.057	ohms
14	Inductance Phase to Phase	L	0.03	mH
15	Mechanical Time Constant	τ_m	1.54	ms
16	Electrical Time Constant	τ_e	0.526	ms

General Data		Symbol	SMX B1210N1026	Unit
17	Gearhead Ratio	-	N/A	Ratio
18	Ambient Working Temperature Range	-	25 (77)	°C (°F)
19	Max Operating Temperature Range	-	155 (311)	°C (°F)
20	Radial Static Force w/o Shaft Support (max)	-	80.28	lbs
21	Axial Static Force w/o Shaft Support (max)	-	27.17	lbs
22	Thermal Resistance	R_{th}	8.7	°C/W
23	Thermal Time Constant	τ_w	975	s
24	Weight	-	267 (9.42)	g (oz)
25	Rotor Inertia	J_m	133 (189)	kg-cm ² 10 ⁻⁴ (oz-in-sec ² 10 ⁻⁶)
26	Hall Sensor Electrical Phasing	-	60	Electrical °
27	Autoclave Cycles	-	1000+	Cycles

- Notes:**
- Three phase motor with Wye connections
 - Hall sensors: supply voltage 4.5 V - 24 V
 - Typical housing material 303 SS
 - Motor type has been designed and tested to achieve the stated number of autoclave cycles
 - Above parameters specified for 25° C ambient temperature
 - Typical shaft material 17-4 PH

Wire	Description
Blue	Phase A
Brown	Phase B
Violet	Phase C
Red	4.5 to 24 Vdc
Yellow	Hall 1
Orange	Hall 2
White	Hall 3
Black	Supply RTN

