


26DAM-K

Ø 26 mm • RoHS Compliant • 33.4 N



Dimensions in mm. [inches]

Electrical Data	26DAMXX•••-K				Unit
	D1B Bipolar	D2B Bipolar	D1U Unipolar	D2U Unipolar	
1 Operating Voltage #	5	12	5	12	VDC
2 Resistance per Phase, ± 10%	14.6	84.0	14.6	84.0	Ohms
3 Inductance per Phase, typ	6.5	33.6	3.8	20.5	mH
4 Rated Current per Phase, 1 Phase ON	0.48	0.20	0.48	0.20	A
5 Input Power	3.4	3.4	3.4	3.4	W

General Data	XX	Linear travel per step	26DAMXX•••-K		Unit
			D1B Bipolar	D2B Bipolar	
6 Min. Holding Force @ rated current	10	@ .001" (0.0254mm)	33.4 (120)	20 (72)	N (oz)
	20	@ .002" (0.0508mm)	25 (90)	15.3 (55)	N (oz)
	40	@ .004" (0.1016mm)	14.5 (52)	8.9 (32)	N (oz)
7 Min. Holding Force (Unenergized)	10	@ .001" (0.0254mm)		20 (72)	N (oz)
	20	@ .002" (0.0508mm)		13.9 (50)	N (oz)
	40	@ .004" (0.1016mm)		5.56 (20)	N (oz)
8 Stroke Length, Typ			13.2 (0.52)		mm (in)
9 Linear Travel Accuracy			± 1 Step		
10 Steps per Revolution			24		
11 Ambient Temperature Range (operating)			-20 to +70 (-4 to +158)		°C (°F)
12 Maximum Coil Temperature			130 (266)		°C (°F)
13 Bearing Type			Ball Bearing		
14 Insulation Resistance at 500 VDC			20		Mohms
15 Dielectric Withstanding Voltage			650 for 2 seconds		VAC
16 Weight			34 (1.2)		g (oz)
17 Leadwire			AWG #28, UL1429 (80° C, 150 V)		

Notes: 1. All motor data values at 20° C unless otherwise specified – 2. # Voltage in case of voltage driver (indicator R•)

