


P532

Ø 52 mm • 205 mNm



Dimensions in mm.

Electrical Data	P532 258 012		P532 258 004		Unit
	10/84 (series)	10/84 (series)	10/84 (parallel)	10/84 (parallel)	
1 Resistance per Phase, typ	27.0	8.8	2.2	0.35	Ohms
2 Inductance per Phase, typ	64.0	20.0	5.0	0.70	mH
3 Nominal Phase Current (2 ph. On)	0.40	0.70	1.40	3.70	A
4 Nominal Phase Current (1 ph. On)	0.56	1.00	2.00	5.20	A
5 Back EMF Amplitude	21.00	12.00	6.00	2.30	V/kstep/s

General Data			
6 Holding Torque, nominal current	205 (29)		mNm (oz-in)
7 Holding Torque, 1.5x nominal current (1)	300 (42.5)		mNm (oz-in)
8 Detent Torque	40 (5.67)		mNm (oz-in)
9 Rotor Inertia	12.000		kgm ² x 10 ⁻⁷
10 Step Angle	3.6		Degree
11 Absolute Accuracy 2 ph. On, Full step mode	+/- 5%		% Full Step
12 Steps Per Revolution	100		
13 Ambient Temperature Range (operating)	-20 to 50 (-4 to 122)		°C (°F)
14 Maximum Coil Temperature	130 (266)		°C (°F)
15 Thermal Resistance Coil-ambient (2)	7.3		°C/W
16 Natural Resonance Frequency (nominal current)	330		Hz
17 Electrical Time Constant	2.30		ms
18 Angular Acceleration (nominal current)	195,000		rad/s ²
19 Bearing Type	Ball		
20 Dielectric Withstanding Voltage	500 VRMS for 5 seconds		VAC
21 Radial Shaft Play	25@5N		µm
22 Axial Shaft Play	25@5N		µm
23 Maximum Radial Shaft Load	20 (72)		N (oz)
24 Maximum Axial Shaft Load (3)	30 (108)		N (oz)
25 Weight	250 (8.8)		g (oz)
26 Power Rate (nominal current)	35.0		kW/s

Notes:

1. Measured with 1 phase ON. The max coil temperature must be respected
2. Motor unmounted
3. Shaft must be supported when press-fitting a pulley or pinion

